



Cluster Connector and Accessories


Purchasing Guide

Purchasing Guide


Factory Fit Cluster Jumpers		Link
K444MW-38S-6	Cluster Jumper Assembly, 4 Port, Cluster-to-4.3-10, 6 FT, WPS	Datasheet
K444MW-38S-8	Cluster Jumper Assembly, 4 Port, Cluster-to-4.3-10, 8 FT, WPS	
K444MW-38S-10	Cluster Jumper Assembly, 4 Port, Cluster-to-4.3-10, 10 FT, WPS	
K444MW-38S-12	Cluster Jumper Assembly, 4 Port, Cluster-to-4.3-10, 12 FT, WPS	
K444MW-38S-15	Cluster Jumper Assembly, 4 Port, Cluster-to-4.3-10, 15 FT, WPS	

Tool Kits		Link
SP-KR-01	Cluster Prep Tool	Datasheet
HCG-INSERTK-38S	Cluster Frameset Insert	Datasheet
JMA-KM-01	Test Adapter, Cluster	Datasheet
KIT-KXR-01	SP-KR-01, HCG-INSERTK-38S, JMA-KM-01	Datasheet
KIT-KXR-FULL-01	KIT-KXR-01 + SP-38S-01 + HCG-FRAMESET-38S	Datasheet

Note
Radio end of cluster jumpers available in all suitable 3/8” Cable Interfaces:
4.3-10, 2.2-5, Nex10, Nex10 Right Angle, 4.3-10 Right Angle, 2.2-5 Right Angle, 4.3-10 Female

KIT-KXR-FULL-01

HCG-Frameset-38S


SP-38S-01


SP-KR-01


HCG-INSERTK-38S



JMA-KM-01

Purchasing Guide

Connector Kits		Link
K4X-H-38S-01	Cluster Housing Kit + 4x UXP-KR-38S-01	Datasheet
K4X-H	Cluster Housing and Blanks (for 2 or 3 jumper configurations)	
JMA38S-50-500	3/8” Superflexible Coaxial Cable, 500ft <i>Also available in 250, 300,350, 500, 450, and 1640 ft</i>	Datasheet

K4X-H

K4X-H-38S-01



Cluster Housing



UXP-KR-38S-01



Cluster Blanks



JMA38S-50

Note
Radio end of cluster jumpers available in all suitable 3/8” Cable Interfaces:
4.3-10, 2.2-5, Nex10, Nex10 Right Angle, 4.3-10 Right Angle, 2.2-5 Right Angle, 4.3-10 Female